







-  PRODUCTS ▾
-  DISTRIBUTOR INVENTORY
-  INDUSTRIES ▾
-  SUPPORT ▾
-  NEWS & EVENTS ▾
-  ABOUT US ▾









2TP216-1-L1

[Products](#) > [Switches](#) > [Rocker Switches](#) > [TP Series](#) > [2TP216-1-L1](#)


Overview

TP Series Rocker Switch, 2 pole, 3 position, Screw terminal, Above Panel Mounting.
 MICRO SWITCH TP Rocker switches may be mounted f
[View More](#)



-  [view all 2TP216-1-L1 literature](#)
-  [view distributor inventory](#)
-  [sample request](#)
-  [email support](#)
-  [get support](#)
-  [email sales](#)
-  [find a distributor](#)
-  [email this page](#)





Technical Specifications

Circuitry	DPDT	Action	3 position
Circuitry/Operating action		Mounting	Above Panel
Lamp Type	Translucent	Termination	Screw
Ampere/Voltage Range (Resistive Load)	0.75 A at 115 Vdc 0.5 A at 250 Vdc 0.5 A to 20 A at 0.5 Vdc to 28 Vdc 0.5 A to 15 A at 0.5 Vac to 277 Vac	Contact Type	Silver Cadmium Oxide Contacts
		LED/Lamp/Neon Voltage	L191: 15 A-125, 250, 277 Vac; 1/2 Hp-125 Vac; 1 Hp-250, 277 Vac; 5 A-120 Vac "L"
Product Type	MICRO SWITCH Rocker		

[View More](#)

View documents in:

Documents

TITLE	DOCUMENT TYPE	LANGUAGE	SIZE
 2TP216-1-L1 highres photo	Photo	--	1MB
 2TP216-1-L1 lowres photo	Photo	--	145KB
 MICRO SWITCH TP Series Rocker Switches Datasheet	Datasheet	English	1MB
 TP Series Rocker Button Switches	Catalog Information	English	391KB

[View More](#)

Product Features

- Environmentally sealed
- Two and three-position pushbutton action
- Various button colors
- 1, 2, and 4-pole circuitry
- Flush panel and above panel mountings
- Temperature range: -54 C to +71 C [-65 F to +160 F]

- UL recognized, CSA certified
- CE approved

Applications

- Industrial machinery and equipment
- Military and commercial aviation
- Marine applications
- Construction equipment
- Test instruments
- Agricultural machinery
- Process control
- Medical instrumentation

NAVIGATION LINKS

[HOME PAGE](#)

[PRODUCTS](#)

[DISTRIBUTOR INVENTORY](#)

[INDUSTRIES](#)

[SUPPORT](#)

[NEWS & EVENTS](#)

[ABOUT US](#)

DISTRIBUTOR LINKS

[ECOM LOGIN](#)

[LEARN CENTER](#)

[REQUEST ACCESS TO ECOM](#)


[SALES/AD PORTAL LOGIN](#)

[SALES/AD PORTAL ACCESS REQUEST](#)

[SAMPLE REQUEST](#)

[SUPPLIER MICROSITE](#)

LANGUAGE

English 

SOCIAL MEDIA



SITE INFORMATION

[PRIVACY STATEMENT](#)

[SITEMAP](#)

[TERMS & CONDITIONS](#)

COPYRIGHT © 2018 HONEYWELL
INTERNATIONAL INC.