

- PRODUCTS ▾
- DISTRIBUTOR INVENTORY
- INDUSTRIES ▾
- SUPPORT ▾
- NEWS & EVENTS ▾
- ABOUT US ▾

914CE2-9

[Products](#) > [Switches](#) > [Limit Switches](#) > [Miniature Limit Switches](#) > [914CE Series](#) > **914CE2-9**

Overview

MICRO SWITCH 914CE Series Compact Precision Limit Switches, Top Roller Plunger, 1NC 1NO SPDT Snap Action, 9 foot Cable.



[View More](#)

Technical Specifications

Availability	Global	Operating Force (OF)	11,8 N [2.65 lb] max.
Release Force	4,4 N [0.99 lb] max.	Pretravel (PT)	1,0 mm ±0,5 mm [0.04 in ±0.02 in]
Overtravel (OT)	3,0 mm [0.118 in] min.	Differential Travel (DT)	0,1 mm [0.004 in] max.
Product Type	MICRO SWITCH Miniature Limit Switches	Actuator	Top Roller Plunger
Termination Type	9 foot Cable	Circuitry	1NC 1NO SPDT Snap Action

[View More](#)

View documents in:

Documents

TITLE	DOCUMENT TYPE	LANGUAGE	SIZE
914CE2-9 highres photo	Photo	English	553KB
914CE2-9 lowres photo	Photo	English	83KB
MICRO SWITCH 914CE Series Compact Limit Switches	Datasheet	English	1MB
XP-4040: 14CE/914CE Series Miniature Limit Switches with UL, CSA and CE approvals	Installation Instructions	English	151KB

[View More](#)

Product Features

- Compact construction
- Pre-wired or connector versions
- Die-cast Zinc housing
- Wide selection of actuators
- Gang mounting capability
- Cable length variations
- Side and bottom exit cable/connector
- Simple two-screw mounting
- Low temperature variants
- Fluorocarbon sealing (standard)

- [view all 914CE2-9 literature](#)
- [view distributor inventory](#)
- [sample request](#)
- [email support](#)
- [get support](#)
- [email sales](#)
- [find a distributor](#)
- [email this page](#)

Applications

- Processing Equipment
- Textile Machinery
- Machine Tools
- Robotics
- Packaging Equipment
- Farm Machinery
- Commercial Laundry Equipment
- Printing Trade Machinery
- Vehicles

NAVIGATION LINKS

[HOME PAGE](#)

[PRODUCTS](#)

[DISTRIBUTOR INVENTORY](#)

[INDUSTRIES](#)

[SUPPORT](#)

[NEWS & EVENTS](#)

[ABOUT US](#)

DISTRIBUTOR LINKS

[ECOM LOGIN](#)

[LEARN CENTER](#)

[REQUEST ACCESS TO ECOM](#)


[SALES/AD PORTAL LOGIN](#)

[SALES/AD PORTAL ACCESS REQUEST](#)

[SAMPLE REQUEST](#)

[SUPPLIER MICROSITE](#)

LANGUAGE

English 

SOCIAL MEDIA



SITE INFORMATION

[PRIVACY STATEMENT](#)

[SITEMAP](#)

[TERMS & CONDITIONS](#)

COPYRIGHT © 2018 HONEYWELL
INTERNATIONAL INC.