

- PRODUCTS ▾
- DISTRIBUTOR INVENTORY
- INDUSTRIES ▾
- SUPPORT ▾
- NEWS & EVENTS ▾
- ABOUT US ▾

V15T16-CZ200

[Products](#) > [Switches](#) > [Basic Switches](#) > [General Purpose Basic Switches](#) > [V15 Series](#) > **V15T16-CZ200**

Overview

MICRO SWITCH V15 Series Standard Basic Switch, 16 A, pin plunger, 6,35 mm x 0,80 mm quick connect terminals, SPDT, 200 gf [1,96 N]. ... [View More](#)



- [view all V15T16-CZ200 literature](#)
- [view distributor inventory](#)
- [sample request](#)
- [email support](#)
- [get support](#)
- [email sales](#)
- [find a distributor](#)
- [email this page](#)

Technical Specifications

| | | | |
|-----------------------|---|----------------------|-----------------|
| Switch Type | MICRO SWITCH Standard 15,9 mm H x 10,30 mm W x 27,80 mm L [0.63 in H x 0.41 in W x 1.09 in L] | Ampere Rating | 16 A |
| Sealed | No | Circuitry | SPDT |
| Actuator | Pin Plunger | Termination | Quick Connect |
| Operating Temperature | -25 °C to 125 °C [-13 °F to 257 °F] | Voltage | 125 Vac/250 Vac |
| Contact Type | Silver Cadmium Oxide | Operating Force (OF) | 200 gf max. |

[View More](#)

View documents in:

Documents

| TITLE | DOCUMENT TYPE | LANGUAGE | SIZE |
|--|------------------|----------|-------|
| V15T16-CZ200 highres photo | Photo | English | 804KB |
| V15T16-CZ200 lowres photo | Photo | English | 87KB |
| MICRO SWITCH V15 Series Standard Basic Switches | Datasheet | English | 2MB |
| Sensors and Switches in Sanitary Valves | Application Note | English | 430KB |

[View More](#)

Product Features

Standard V-Basic Switch Features

- Best suited for lower cost-of-failure applications
- Designed from 10K to 50K operations at a full load or 5M for mechanical life
- World-wide package size acceptance
- Current rating ranges of 10 A and 26 A
- UL/CSA, cUL, ENEC, and CQC approvals

Applications

- Appliance
- Gaming
- Vending machines
- Water heaters
- Industrial controls

NAVIGATION LINKS

[HOME PAGE](#)

[PRODUCTS](#)

[DISTRIBUTOR INVENTORY](#)

[INDUSTRIES](#)

[SUPPORT](#)

[NEWS & EVENTS](#)

[ABOUT US](#)

DISTRIBUTOR LINKS

[ECOM LOGIN](#)

[LEARN CENTER](#)

[REQUEST ACCESS TO ECOM](#)


[SALES/AD PORTAL LOGIN](#)

[SALES/AD PORTAL ACCESS REQUEST](#)

[SAMPLE REQUEST](#)

[SUPPLIER MICROSITE](#)

LANGUAGE

English 

SOCIAL MEDIA



SITE INFORMATION

[PRIVACY STATEMENT](#)

[SITMAP](#)

[TERMS & CONDITIONS](#)

COPYRIGHT © 2018 HONEYWELL
INTERNATIONAL INC.