CATALOG LISTING THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH. A DIVISION OF MICRO SWITCH RAILWAY CLAMP HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH RDS-CL-01 a Honeywell Division (SINGLE MOUNT) FED. MFG. CODE 91929 RDS-CL-01 SENSOR CLAMP MOUNTING BOLTS FE-33318 능 RAIL CLAMP MOUNTING BOLTS 2.1 2.0 1.0 (11.600)D 0002417 JLH 22DEC03 RAIL CLAMP MOUNTING BOLTS **MECHANICAL SPECIFICATIONS:** OPERATING TEMPERATURE: -40°C TO 85°C SHOCK: 500g, HALFSINE 1.6 mSEC (IEC68-2-27) NOTES \oplus =1 DESIGNED TO BE MOUNTED ON RAILS : VIBRATION: SINUSOIDAL 10-2000 Hz, 20G, (IEC68-2-6) 119RE, 132RE, 133RE, 136RE, AND 140RE SCALE NONE 2 RAIL SECTION SHOWN FOR ILLUSTRATION 30 MINUTES EACH AXIS FOR DO NOT SCALE PRINT TEMPERATURES -40°C, 25°C, AND 85°C PURPOSES ONLY UNLESS OTHERWISE SPECIFIED TOLERANCES ARE **MOUNTING TORQUE:** ONE PLACE (.0) ±.030 TWO PLACE (.00) ±.015 RAIL CLAMP MOUNTING BOLTS: 60 FT-LBS THREE PLACE (.000) ±.005 SENSOR CLAMP MOUNTING BOLTS: 7 FT-LBS ANGLES WEIGHT ANSI Y14.5M-1982 APPLIES