




HONEYWELL
PART NUMBER

-

REV	DOCUMENT	CHANGED BY	CHECK
4	0041144	SS 26JUN08	BLR



RELEASE NO. PR-17367	CATALOG LISTING CW-B5541
REPLACES	

CHARACTERISTICS
OPERATING FORCE-----150 GRAMS MAX
RELEASE FORCE----- 25 GRAMS MIN
DIFFERENTIAL TRAVEL----- .002- .010
OVERTRAVEL----- .030 MIN
FREE POSITION----- .675 MAX
RELEASE TRAVEL----- .010 MIN

ELECTRICAL DATA
CONTACT ARRANGEMENT S P N O
L215
15.1A 1/2HP 125, 250 OR 277 VAC 1/2A 125 VDC
1/4A 250 VDC; 5A 125 VAC "L"

DESIGN UNITS: INCH
TOLERANCES UNLESS NOTED:
NO PLACES X ± -
ONE PLACE .X ± 0.030
TWO PLACE .XX ± 0.015
THREE PLACE .XXX ± 0.005
ANGLES X ± -
THIRD ANGLE PROJECTION

DRAWN	JAS	12JUN89
CHECK	JAP	14JUN89
THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.		
INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY		

Honeywell				
TITLE SWITCH, BASIC				
SIZE	TYPE	CAGE CODE	DRAWING NAME	REV
B	I	-	V7-1C27D8-000-1	4
SCALE	-		SHEET	1 OF 1