

# MICRO SWITCH

FREEPORT ILLINOIS, U S A  
A DIVISION OF HONEYWELL  
FED. MFG. CODE 9 1929

## SWITCH-BASIC

CATALOG LISTING

V7-5F17D8-000-1

CW-C5008

V7-5F17D8-000-1

REPLACES X86002-V7

RELEASE NO. PR-15367

**M**

DRAWING NUMBER

ISSUE  
X 5

REVISIONS

|   |          |       |            |
|---|----------|-------|------------|
| A | CO62202  | J A P | 24 MAY 88  |
| B | CO63974  | L J F | 3 AUG 88   |
| C | CO66350  | J A P | 18 SEPT 89 |
| D | CO 78108 | L J F | 21 OCT 93  |

CHECK

CHECK

CHECK

CHECK

CHECK



CHECK

CHECK

CHECK

CHECK

CHECK



THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH. A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION

**CHARACTERISTICS**

OPERATING FORCE-----8 GRAM MAX  
  
RELEASE TRAVEL-----.010 MIN  
DIFFERENTIAL TRAVEL-----.002-.010  
OVERTRAVEL-----.050 MIN  
FREE POSITION-----.625 MAX

**ELECTRICAL DATA**

CONTACT ARRANGEMENT  
S P D T

3A 125, 250, 277 VAC  
1/10 HP 250 VAC

L 163



SCALE FULL

DO NOT SCALE PRINT

TOLERANCES  
APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE UNLESS NOTED. TOLERANCES ARE ±

|              | DIM.<br>mm | TOL.<br>mm/in | DIM.<br>in | TOL.<br>mm/in |
|--------------|------------|---------------|------------|---------------|
| NO PLACES    | X          | 17 04         | X X        | 0.01/00       |
| ONE PLACE    | X,X        | 0.4/016       | X X X      | 0.38/016      |
| TWO PLACES   | X,X,X      | 0.15/006      | X X X X    | 0.13/006      |
| THREE PLACES | X,X,X,X    |               | X X X X X  |               |
| ANGLES       |            |               |            |               |

DESIGN UNITS  SI METRIC  US CUSTOMARY

WEIGHT

FO-52848-A

DRAWN

S. J. S. 30 JAN 87