

Honeywell Sensing and Control

Search



V7-7B17D8-481
 (Home : Products : Switches » MICRO SWITCH™ Basic Switches » Premium V-Basic Switches » V7)

[contacts](#)

narrow your search

Products

- Controls Monitoring and Lighting (286)
- Machine Safety (1727)
- Sensors (6165)
- Switches (9781)
- Wireless (45)

Technology

- Control and Instrumentation (890)
- Electromechanical (9307)
- Magnetic (541)
- Platinum thin film (56)
- Thick Film (1372)
- More...

new products

New Wireless Products

Go farther. Work smarter. Explore new possibilities. Just by cutting the cord and making the switch.



Wireless Web Site
 WGLA and WPMM
 XYR6000™

[find out more](#)

white papers

- Wireless Switches Offer Unlimited Benefit
- Basic Switches Are Not Created Equal
- Applying Precision Switches
- Sensors for Medical Devices
- New Ways to Measure Torque
- Choosing Safety Switches
- Specifying Hour Meters

Need help?

[Click here to contact us](#)



Actual product appearance may vary.

V7 Series Miniature Basic Switch, Single Pole Double Throw Circuitry, 11 A at 250 Vac, Curved Tip Actuator, 178 gf Maximum Operating Force, Silver Contacts, Quick Connect Termination

[Sales & Service](#)

[Distributor Inventory](#)

[Overview](#) [Specs](#) [Documentation](#) [Application Notes](#)

Product Specifications

Switch Type	MICRO SWITCH™ Miniature 15,9 mm H x 10,2 mm W x 28,8 mm L [0.63 in H x 0.4 in W x 1.14 in L]
Sealed	No
Ampere Rating	11 A
Circuitry	SPDT
Actuator	Curved Tip Lever
Termination	Quick Connect
Operating Temperature	-40 °C to 85 °C [-40 °F to 185 °F]
Voltage	250 Vac
Actuator Length	19,4 mm [0.76 in]
Contact Type	Silver
Operating Force (OF)	178 gf max.
Release Force	28 gf min.
Pretravel (PT)	2,16 mm [0.085 in] max.
Overtravel (OT)	1,3 mm [0.051 in] min.
Differential Travel (DT)	0,50 mm [0.020 in] max.
Operating Position (OP)	19,51 mm ±1,02 mm [0.768 ±0.040 in]
Housing Material	PCT Polyester Thermoplastic
Agency Approvals and Standards	UL, CSA
Mounting Centers	22,2 mm [0.88 in]
Tightening Torque	0,56 N m [5.0 in lb]
Weight	8 g [0.3 oz]
Package Height	15,9 mm [0.63 in]
Package Width	10,3 mm [0.40 in]
Package Length	27,8 mm [1.09 in]
Comment	CE: 61058-1; UL: E12252; CSA: LR41370
Availability	Global
UNSPSC Code	30211905
UNSPSC Commodity	30211905 Snap switches
Series Name	V7

- Customer Service
- Technical Support
- Global Sales & Service
- View Site Demo
- Site Comments?

meet dr. larry

VIDEO - Dr. Larry Goldstein explains our newest and best technologies.



Meet Dr. Larry

my links

- [Login to iCOM](#)
- [Login to Rep/AD Portal](#)
- [Login to Digital University](#)

News Center

- Honeywell Introduces TruStability® NSC Series, Uncompensated / Unamplified Board Mount Pressure Sensors
- HONEYWELL EXPANDS ITS LIMITLESS™ PLATFORM WITH THE LAUNCH OF ITS GLOBALLY AVAILABLE INDUSTRIAL WIRELESS RECEIVER
- HONEYWELL INTRODUCES MICROPOWER OMNIPOLAR DIGITAL HALL-EFFECT SENSOR ICS WITH LOW SUPPLY VOLTAGE AND ULTRA LOW TYPICAL CURRENT
- HONEYWELL EXTENDS ITS TRUSTABILITY® PRESSURE SENSOR PRODUCT LINE WITH A SINGLE SIDE LIQUID MEDIA OPTION
- HONEYWELL ADDS NEW 100° AND 180° ARC CONFIGURATIONS TO ITS SMART POSITION SENSOR PORTFOLIO
- HONEYWELL INTRODUCES ITS HAWK™ RESOLVERS 1-INCH SERIES, FULLY HOUSED CONFIGURATION

[MICRO SWITCH Anniversary site](#)