

BU-P3925-@
(Standard Plunger Clip, Small Wire)



- The BU-P3925 is a standard plunger clip. It can be installed to wire up to 20 AWG with a jacket as large as ϕ .09" (2.3 mm). Hook attaches to leads up .060" (1.5mm). See Part number BU-P4555-@ for a large wire version
- Easy solder connection
- Material: Contact Beryllium Copper
 Spring 304 Stainless Steel
 Housing Glass filled Nylon
- Overall length 2.35" (59.7mm), Hook ID = .09" (2.3mm)
- Ratings:
 - Current: 5 Amps
 - Voltage: Hands free testing to 300 VRMS.
 - Operating Temperature: -40°F (-40°C) to 221°F (105°C)
- Color: The "@" in the model number indicates color.
 Available colors are: -0 Black, -2 Red, -4 Yellow, -5 Green, -6 Blue, -9 White
- RoHS Compliant