



BU-00000-*
Part # color

* 0 - Black 5 - Green
2 - Red 6 - Blue
4 - Yellow 9 - White

Test Leads Page 1

1 | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9 | 10 | 11 | 12 | 13 | 14 | 15 | 16 | 17 | 18 Page 3

BU-1420-A-00-*

"Mini-Micro-Plunger" To Stackable Banana Plug

- Mini-Micro-Plunger (No. 208)
- Gold-plated one-piece beryllium copper conductor.
- Nylon stem and cap; stainless steel compression spring.
- Attaches to 0.025" (.6mm) dia. and smaller leads
- Nine-leaf, beryllium copper, nickel-plated conductor provides positive contact.
- Hook-up Wire: #20 AWG (41/36)tinned copper with 105°C PVC insulation.
- [Product Data Sheet & Compatibility Info.](#)
- [Send us your questions about this product](#)



BU-1421-A-00-*

"Mini-Micro-Plunger" To Shrouded Banana Plug

- No. 208 Spring-loaded beryllium copper plunger hook.
- Safety shrouded four-leaf conventional banana plug with nickel-silver plating.
- Stainless steel compression string.
- #20 AWG wire (41/36) tinned copper with 105°C PVC insulation.
- [Product Data Sheet.](#)
- [Send us your questions about this product](#)



"Mini-Plunger" To Stackable Double Banana Plug

BU-1170-C-00-0 with RG58

BU-1170-F-00-0 with RG174

- Spring-loaded, beryllium copper conductor.
- Red (+) plungers, 3" (76 mm) lead wires.
- Black (-) plungers, 8" (203 mm) lead wires.
- Molded "Y" prevents separation and corrosion.
- Nine-leaf, beryllium copper, nickel-plated spring.
- Shielded RG58C/U, MIL-C-17F, 50 ohm or shielded RG174/U, MIL-C-17D, 50 ohm coaxial cable.
- [Product Data Sheet](#)
- [Send us your questions about this product](#)



Enlarge

"Mini-Plunger" To BNC Male
BU-1150-C-00-0 with RG58
BU-1153-F-00-0 with RG174

- Spring-loaded beryllium copper conductor, (No. 202)
- Red (+) plunger, 3" (76 mm) lead wire.
- Black (-) plunger, 8" (203 mm) lead wire.
- Molded "Y" prevents separation and corrosion.
- BNC Male Connector: MIL-C-30912 has gold-plated center contact and silver-plated body.
- RG174/U BNC is a commercial connector with nickel-plated body.
- Shielded RG58C/U, MIL-C-17F, 50 ohm or shielded RG174/U, MIL-C-17D, 50 ohm coaxial cable.
- [Product Data Sheet](#)
- [Send us your questions about this product](#)



[Enlarge](#)

[Contents](#)|[Next](#)

[Home](#)|[Insulated BNCs](#)|[Clips & Insulators](#)|[Insulated Test Accessories](#)
[Accessories & Probes](#)|[Kits](#)|[Cross Reference](#)

©1999-2000 Mueller Electric Company. All rights reserved.
Problems with the site should be reported to the [webmaster](#).