

Resonators > CERALOCK (MHz) > Series













How to check EU RoHS Compliant of Our Products is [here](#).

Product Lifecycle Stage	in Production
Recommended Rank	Preferred

Specification

Global Part Number	CSTLS_G
Previous Part Number	CSTS_MG
Oscillating Frequency	3.40 to 10.00MHz
Initial Tolerance	±0.5%
Temp. Stability	±0.2% [-0.4% to +0.2%:Built-in Capacitance 47pF type]
Temperature Range	-20 to 80°C
Wash	Not Available
Ultrasonic Wash	Not Available
Capacitor	Built in
Frequency Tolerance	Available in ±0.3%,±0.2%
Use	
Applications	For consumer electronics

Details

- ?  [Part Numbering](#)
- ?  [Appearance](#)
- ?  [Dimensions](#)
- ?  [Features, Applications](#)
- ?  [Temperature Characteristics](#)
- ?  [Basic Oscillation Circuit](#)
- ?  [Notice \(storage and operating condition\)](#)
- ?  [Notice \(rating\)](#)
- ?  [Notice \(soldering and mounting\)](#)
- ?  [Notice \(handling\)](#)
- ?  [Packaging](#)
- ?  [Minimum Quantity\[Supplementation\]](#)

Minimum Quantity

180mm Paper Tape	
180mm Embossed Tape	
330mm Paper Tape	
330mm Embossed Tape	
Bulk Case	
Bulk(Bag)	500
Ammo Pack	2000
320Reel	
Magazine	
Box	

Please approve our product specifications or to transact the approval sheet for product specifications before ordering. Please read rating and !Cautions first.
Product specifications in this catalog are as of January 2008.

All products and company names herein are trademarks or registered trademarks of their respective owners.