



- Home
- About Us
- Products**
- Audio
- Video
- Lighting
- Data Connectors
- Industrial

- Support
- News
- Sitemap

Search

PRODUCTS ONLY

Search

© Neutrik® AG
All rights reserved
Legal Notices



Audio

Circular Adapters

[back](#)

NA3MM

Product

Connector Type Adapter

Electrical

Contact resistance $\leq 3 \text{ m}\Omega$

Dielectric strength 1,5 kVdc

Insulation resistance $> 2 \text{ G}\Omega$

Mechanical

Locking device Latch lock

Material

Contact plating 2 μm Ag

Contacts Brass (CuZn39Pb3)

Insert Polyamide (PA 6.6 30 % GR)

Shell Zinc diecast (ZnAl4Cu1)

Shell plating gal Cu/Ni

Environmental

Temperature range -20 °C to +65 °C