



Deutsche Version

[Home](#)

[About Us](#)

**Products**

[Audio](#)

[Video](#)

**Lighting**

[Data Connectors](#)

[Industrial](#)

[Support](#)

[News](#)

[Sitemap](#)

Search

PRODUCTS ONLY

Search

© Neutrik® AG  
All rights reserved  
[Legal Notices](#)



Lighting

## DMX Adapters

[back](#)

NA3M5F

### Product

Connector Type Adapter

### Electrical

Contact resistance < 3 mΩ

Dielectric strength 1,5 kVdc

Insulation resistance > 2 GΩ

Rated current per contact 7,5 A

### Mechanical

Insertion force < 20 N

Withdrawal force < 20 N

Lifetime > 1000 mating cycles

Locking device Latch lock

### Material

Contact plating 2 μm Ag

Contacts Brass (CuZn39Pb3)

Insert Polyamide (PA 6.6 30 % GR)

Shell Zinc diecast (ZnAl4Cu1)

Shell plating Nickel

### Environmental

Temperature range -30 °C to +80 °C