



## NAC3FCB

Lockable cable connector, power-out, screw terminals, grey

The powerCON is a locking 3 conductor equipment AC connector with contacts for line, neutral and pre-mating ground contact. It replaces appliance couplers wherever a very rugged solution in combination with a locking device is needed in order to guarantee a safe power connection.

**Attention:** The powerCON is a connector without breaking capacity, i.e. the powerCON should not be connected or disconnected under load or live!

### Features & Benefits

- Power-in (blue) and power-out (grey) versions with different keying to avoid the possibility of intermating
- Extremely robust and reliable
- Unique Neutrik chuck type strain relief
- UL, cUL recognized components  
VDE certified  
SEV approved
- Fast and easy twist lock latching system
- Ergonomic design
- Improved kink protection by two-component bushing
- Branded with unique hologram - guarantees genuine and authentic Neutrik product

## Technical Information

Product	
Title	NAC3FCB
Gender	female

Electrical	
Contact resistance	≤ 3 mΩ
Dielectric strength	4 kVdc / 2.8 kVac
Insulation resistance	> 0.1 GΩ (after damp heat test IEC 68-2-30)
Number of electrical contacts	2 + PE
Rated current per contact	20 A rms
Rated voltage	250 V ac

Mechanical	
Cable O.D.	6 - 15 mm (1)
Lifetime	> 1000 mating cycles
Wiresize	2,5 mm <sup>2</sup>
Wiresize	12 AWG
Locking device	Quick Lock
(1)	Cable O.D. range limited to 6 mm - 14 mm acc. VDE

Material	
Contact plating	4 μm Ag
Contacts	Bronze (CuSn6)
Insert	Polyamide (PA 6 30 % GR)
Locking element	Zinc diecast (ZnAl4Cu1)
Shell	Polyamide (PA 6 30 % GR)
Strain relief	Polyacetal (POM)

Environmental	
Temperature range	-30 °C to +80 °C

