

# NE8FDY-C6

The etherCON CAT6 D-shape panel connectors with metal housing and secure latching system offer a tool-free and gas-tight IDC termination, which makes cable assembly easy and fast.







### Features & Benefits

- CAT6 compliant - data rate up to 10 GBit/s
- CAT6 performance - fast data transmission and high bandwidth applications
- CAT6 specifications according TIA / EIA 568B, ISO / IEC 11801, EN 50173
- IP65 - Dust and waterproof in mated condition
- Shielded system - high noise immunity and EMI protection
- Push Pull mating - secure and proven locking system
- Ground lead jumper on panel connector with selectable grounding option
- Gas-tight IDC termination without tool

Technical Information [show](#)

### Accessories

<p>DSS-*</p> 	<p>MFD</p> 	<p>SCDP-*</p> 	<p>SCDX</p> 	<p>SCCD-W</p> 
<p>SCD-W</p> 				

### Downloads

- Assembly Instruction - etherCON CAT6 Chassis Connector
- Expert's report etherCON CAT6 IP65
- Product Guide - Section Data Connectors
- 3D File NE8FDY-C6
- Drawing NE8FDY-C6
- Drawing NE8FDY-C6