

ZR0207 Product Details

[Live Product Chat](#)



Fixed Resistors

[Converted to EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- ZR Series
- Resistance Selection = <1K Ω
- Resistance = 0 Ω
- Power Rating = .30 W
- Tolerance = 0 %

[View all Features](#) | [Find Similar Products](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

NEW!

ZR0207
(1623934-1)

TE Part Number: 1623934-1

[Active](#)

[Add to Part List](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- [Zerohm Links - Type ZR Series - Tyco Electronics Pas...](#) (PDF, English)

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Resistance \(\$\Omega\$ \)](#) = 0
- Resistor Type = Zerohm Link
- [Element](#) = Foil
- [Termination Type](#) = Tinned Copper Leads
- Comment = Tolerance = 0.002 Ohms

Electrical Characteristics:

- [Resistance Selection \(\$\Omega\$ \)](#) = <1K
- [Tolerance \(%\)](#) = 0
- [Package Type](#) = Ammo Packed

Body Related Features:

- [Series](#) = ZR
- [Power Rating \(W\)](#) = 0.30
- [Mount Style](#) = Axial Leaded
- [Packaging Style](#) = 0207
- [Package, Component Size](#) = 5.6 x 2.3

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Converted to comply with RoHS directive

Operation/Application:

- [Application](#) = Zero Ohm Link

Other:

- Brand = Neohm