

NTE Electronic Components

- [Cable/Wire-Ties](#)
- [Capacitors](#)
- [Circuit Protection](#)
- [Clips/Test Leads](#)
- [Fuses](#)
- [Heat Shrink Tubing](#)
- [Hook Up Wire](#)
- [LED Tubing](#)
- [Optoelectronic Devices](#)
- [Pots/Trimmers/Knobs/
Dials](#)
- [Relays](#)
- [Resistors](#)
- [Semiconductors](#)
- [Solder Wick](#)
- [Switches](#)
- [NEW! Terminals &
Connectors](#)

ECG Consumer/ Commercial Products

- [Antenna Rotors](#)
- [Chemicals](#)
- [Heat Guns](#)
- [Infrared Thermometer](#)
- [Solder Irons, Butane/
Electric Corded](#)
- [Surge Protectors](#)
- [Test Equipment](#)
- [Wireless Security &
Inspection Cameras](#)

Master Distributed Lines

- [Amphenol RF: Connectors](#)
- [CML: Optoelectronic
Products](#)
- [Coast: LED Flashlights](#)
- [Connex: RF Connectors](#)
- [ITW-DYMON: Scrubs,
Premoistened Wipes](#)
- [Kester Solder Products](#)
- [Plato: Replacement
Solder Iron Tips](#)
- [Techspray: Chemicals](#)

Solder Wick

NTE Solder Wick is made from fine copper wire woven together with a no-clean flux formula added to it to increase absorption.

- Removes up to four times more solder than conventional wick, and extracts solder much faster than wicks based on Type-R fluxes.
- Residue left behind is halide free and non-conductive, so it does not have to be cleaned off the board.
- 100% copper wick has fine braid design to promote strong capillary action to pull in excess solder.
- Available with standard or anti-static bobbins.



Solder Wick

Description	NTE Part No.
No-Clean Wick, #3 Green, Width .075" (1.9mm), Length 5 ft.	SW01-5
No-Clean Wick, #3 Green, Width .075" (1.9mm), Length 10 ft.	SW01-10
No-Clean Wick, #3 Green, Width .075" (1.9mm), Length 25 ft.	SW01-25
No-Clean Wick, #3 Green, Width .075" (1.9mm), Length 50 ft.	SW01-50
No-Clean Wick, #4 Blue, Width .098" (2.5mm), Length 5 ft.	SW02-5
No-Clean Wick, #4 Blue, Width .098" (2.5mm), Length 10 ft.	SW02-10
No-Clean Wick, #4 Blue, Width .098" (2.5mm), Length 25 ft.	SW02-25
No-Clean Wick, #4 Blue, Width .098" (2.5mm), Length 50 ft.	SW02-50
No-Clean Wick w/Anti-Static Bobbin, #3 Green, Width .075" (1.9mm), Length 5 ft.	SW03-5
No-Clean Wick w/Anti-Static Bobbin, #3 Green, Width .075" (1.9mm), Length 10 ft.	SW03-10
No-Clean Wick w/Anti-Static Bobbin, #3 Green, Width .075" (1.9mm), Length 25 ft.	SW03-25
No-Clean Wick w/Anti-Static Bobbin, #3 Green, Width .075" (1.9mm), Length 50 ft.	SW03-50
No-Clean Wick w/Anti-Static Bobbin, #4 Blue, Width .098" (2.5mm), Length 5 ft.	SW04-5
No-Clean Wick w/Anti-Static Bobbin, #4 Blue, Width .098" (2.5mm), Length 10 ft.	SW04-10
No-Clean Wick w/Anti-Static Bobbin, #4 Blue, Width .098" (2.5mm), Length 25 ft.	SW04-25
No-Clean Wick w/Anti-Static Bobbin, #4 Blue, Width .098" (2.5mm), Length 50 ft.	SW04-50

[Back](#)

- [Home](#)
- [Contact](#)
- [About](#)
- [Distributor Locator](#)
- [FAQs](#)
- [Literature](#)



Follow NTE on
Facebook and Twitter