



◆ **HG-001VT Economy Model:**

Compact, lightweight, easy to use

◆ **HG-002/003/005 Industrial Grade Models:**

Rugged performance, prolonged use, lighter than other similar models

◆ **Diffuser Nozzles**

A variety of diffuser nozzles are available for different applications

- Reflectors
- Concentrators

ECG[®]

HEAT GUNS



Features:

- **General Heating and Drying**
- **Melt Plastics**
- **Bend Plastic & Laminates**
- **Shrink Film Packaging**
- **Smooth Vinyl Wrinkles**
- **Shrink Terminals/Tubing**
- **Soften Floor Tile**
- **Thawing Frozen Locks**

PRODUCT/APPLICATION INFORMATION

HG-001VT ELECTRIC HEAT GUN

- General purpose heat gun
- Electronic variable temperature control dial with temperatures ranging from 250°F - 1100°F/ 120°C - 590°C
- Built-in safety handle
- Two speed motor
- Solid state construction
- High quality heat element
- Heat Guard
- Strips paint and varnish
- Thawing or drying
- Shrinking/softening
- Perfect for hobbyists, DIY enthusiasts, engineers, electricians, automotive and marine repair

SPECIFICATIONS

Volt: 120
Amp: 10
Low Temp.°F: 250
High Temp.°F: 1100
Watts: 1200

* 6 month warranty

HG-002/003/005 HEAT GUNS

- Fast controlled flameless heat
- Variable temperature adjustment (models 200° - 750°F)
- Molded components of impact resistant GE[®] Lexan
- Long life break resistant mica heating element
- Adjustable air intake regulator
- Double jacketed nozzle and shield
- Toggle type control switch
- Nozzle air opening
- 50/60 cycle AC motor
- 6 ft. three wire grounding type strain relief cord
- Circular safety stand for ease of handling
- Superior air flow
- Weighs less than 3 lbs
- Replaceable brushes
- Paint stripping
- Thawing or drying
- Shrinking/softening
- Optional application accessories

SPECIFICATIONS

	HG-002	HG-003	HG-005
Volt:	115	115	115
Amp:	9	9	12
Low Temp.°F:	200	300	500
High Temp.°F:	300	500	750

* 1 year warranty includes element breakage

DIFFUSER NOZZLES:



- For HG-002/003/005 Heat Guns:
 - **HG-0010:** 3/4" reflector
 - **HG-0011:** 2" reflector
 - **HG-0012:** pinpoint concentrator
- For HG-001VT Electric Heat Gun:
 - **HG-0013:** 7/8" heat concentrator
 - **HG-0014:** 3/8" pinpoint concentrator
 - **HG-0015:** shrink tube reflector

