

UNSHIELDED PLASTIC or TPE JACKETED MINIATURE CORDS UL LISTED



Stranded tinned copper, polypropylene insulated, black PVC jacketed.
-20°C +80°C

OLYMPIC NO.	AVAIL. LENGTHS (RETRACTED) (INCHES)	NO. OF COND.	AWG NO.	MAX WORKING VOLTAGE	STRAND NO./AWG	COND. AMP RATING	CABLE O.D. (INCHES)	COIL O.D. (INCHES)
6516P	48,36,24,12	2	28	300	7/36	1/2	.140	1/2
6517P	48,36,24,12	3	28	300	7/36	1/2	.150	1/2
6518P	48,36,24,12	4	28	300	7/36	1/2	.155	1/2
6519P	48,36,24,12	5	28	300	7/36	1/2	.165	9/16
6520P	48,36,24,12	6	28	300	7/36	1/2	.180	5/8
6521P	48,36,24,12	7	28	300	7/36	1/2	.180	5/8
6522P	48,36,24,12	8	28	300	7/36	1/2	.195	5/8
RETRACTED - EXTENDED RATIO (1 TO 5)								
48" - 20'		36" - 15'		24" - 10'		12" - 5'		
STRAIGHT LEAD LENGTHS								
6"		6"		6"		12"		

UNSHIELDED PLASTIC or TPR JACKETED COMMUNICATIONS & ELECTRONIC CONTROL CORDS



UL LISTED

Stranded tinned copper, polypropylene insulated, PVC or TPR jacketed.
-20°C +80°C

OLYMPIC NO.	AVAIL. LENGTHS (RETRACTED) (INCHES)	NO. OF COND.	AWG NO.	MAX WORKING VOLTAGE	NOM. AREA (mm)	STRAND NO./AWG	COND. AMP RATING	CABLE O.D. (INCHES)	COIL O.D. (INCHES)
* 6370P	48,36,24,12	2	23	300	.259	21/36	1	.180	5/8
** 6382P									
* 6371P	48,36,24,12	3	23	300	.259	21/36	1	.190	11/16
** 6383P									
* 6372P	48,36,24,12	4	23	300	.259	21/36	1	.200	11/16
** 6384P									
* 6373P	48,36,24,12	5	23	300	.259	21/36	1	.215	3/4
** 6385P									
* 6374P	48,36,24,12	6	23	300	.259	21/36	1	.230	7/8
** 6386P									
* 6375P	48,36,24,12	7	23	300	.259	21/36	1	.230	7/8
** 6387P									
* 6376P	48,36,24,12	8	23	300	.259	21/36	1	.245	7/8
** 6388P									
* 6377P	48,36,24,12	10	23	300	.259	21/36	1	.280	15/16
** 6389P									
* 6378P	48,36,24,12	12	23	300	.259	21/36	1	.285	1
** 6390P									
* 6379P	48,36,24,12	15	23	300	.259	21/36	1	.310	11/16
** 6391P									

*Black PVC jacket
**Black TPR jacket