

[All Categories](#) > [Control Components](#) > [Timers](#) > [Time-Delay Relays](#) > [H3Y-B](#) > Item # H3Y-2-B AC100-120 10S

Item # H3Y-2-B AC100-120 10S, 0.5, 10 s Time Range Timer

Request Information

[Printable Page](#) [Download PDF](#) [Email This Page](#)



Timer DPDT Black 10 sec

DOWNLOADS

[H3Y-B, H3YN-B
Miniature Timers, Push-
In Plus Terminal Sockets
Datasheet](#)

Specifications

Type	Timer
Output Type	Double Pole Double Throw (DPDT)
Time Range	0.5, 10 s
Dependencies	PYF-08-PU-L
Accessories	PFP
Display	Light Emitting Diode (LED) Indicator
Setting Method	Analog Dial
Reset Method	Self Reset
ON-Delay Mode	Yes
Repeat Cycle OFF Start Mode	No
Repeat Cycle ON Start Mode	No
Repeat Cycle, Independent ON/OFF Times	No
Signal ON/OFF Delay ON Start Mode	No
Signal ON/OFF Delay OFF Start Mode	No
Signal OFF Delay Mode	No
Interval Mode	No
One-Shot Output Mode	No

Power OFF Delay	No
Power ON Delay	No
ON/OFF Adjustable Duty Cycle	No
Twin Timer	No
Stopwatch	No
Cumulative	No
On-Delay with Instantaneous Output	No
Star-Delta	No
Inputs	No Inputs
Connection Type	8 Pin Socket
Alternating Current (AC) Supply Voltage	100 to 120 V
Height	28 mm
Width	21.5 mm
Depth	56.6 mm
Number of Operating Modes	1

News

[Product News](#)
[Corporate News](#)
[Omron on Social Media](#)
[eNews](#)

Company Info

[About Omron](#)
[Omron Principles](#)
[Company Profile](#)
[Business Fields](#)
[Events](#)
[Giving Back](#)
[Environmental](#)





Careers

[Awards](#)
[Giving Back](#)
[Summer Internships](#)

Contact

[Omron in United States](#)
[Contact Us](#)
[Global presence](#)

Follow us

 [Facebook](#)
 [Twitter](#)
 [LinkedIn](#)
 [Youtube](#)