

[All Categories](#) > [Control Components](#) > [Timers](#) > [Analog-Set Solid State Timers](#) > [H3DT](#) > Item # H3DT-G AC/DC24-240

Item # H3DT-G AC/DC24-240, 1.0, 120 s Time Range Timer

Request Information

[Printable Page](#) [Download PDF](#) [Email This Page](#)



TwinTm DPDT ACDC 24-240V Push In

DOWNLOADS

[H3DT Slim Track Mount Timers with Push-In Plus Terminals Datasheet](#)

Specifications

Type	Timer
Terminal Type	Push-In Plus Terminals
Output Type	Double Pole Double Throw (DPDT)
Time Range	1.0, 120 s
Accessories	Y92A-D1A, PFP
Display	Light Emitting Diode (LED) Indicators
Setting Method	Analog Dial
Reset Method	Self Reset
ON-Delay Mode	No
Repeat Cycle OFF Start Mode	No
Repeat Cycle ON Start Mode	No
Repeat Cycle, Independent ON/OFF Times	No
Signal ON/OFF Delay ON Start Mode	No
Signal ON/OFF Delay OFF Start Mode	No
Signal OFF Delay Mode	No
Interval Mode	No
One-Shot Output Mode	No

Power OFF Delay	No
Power ON Delay	No
ON/OFF Adjustable Duty Cycle	No
Twin Timer	Yes
Stopwatch	No
Cumulative	No
On-Delay with Instantaneous Output	No
Star-Delta	No
Up Display On-Delay	No
Down Display On-Delay	No
Alternating Current (AC) Supply Voltage	24 to 240 V
Direct Current (DC) Supply Voltage	24 to 240 V
Number of Operating Modes	1

News

Product News
 Corporate News
 Omron on Social Media
 eNews

Company Info

About Omron
 Omron Principles
 Company Profile
 Business Fields
 Events
 Giving Back
 Environmental





Careers

Awards
 Giving Back
 Summer Internships

Contact

Omron in United States
 Contact Us
 Global presence

Follow us

 Facebook
 Twitter
 LinkedIn
 Youtube