

[All Categories](#) > [Automation Control Systems](#) > [Machine Automation Controllers](#) > [NJ Series Controllers](#) > [NJDIGIO](#) > Item # CJ1W-ID211 (SL)

## Item # CJ1W-ID211 (SL), 16 Input/Output (I/O) Capacity Input Unit

[Request Information](#)

[Printable Page](#) [Download PDF](#) [Email This Page](#)



CJ 16 Point 24 VDC NPN/PNP input unit

### Specifications

Type	Input Unit
Number of Inputs	16
Terminal Type	Screwless
Input/Output (I/O)	16
Number of Machine Units	1
Number of Inputs Per Common	16
Input ON Time (Selectable)	0.02 to 32 ms
Input OFF Time (Selectable)	0.4 to 32 ms
DC Input Voltage	24 V
Current Consumption at 5 VDC	0.08 A
Input Current	10 mA
Module Width	31 mm

#### News

[Product News](#)  
[Corporate News](#)  
[Omron on Social Media](#)  
[eNews](#)

#### Company Info

[About Omron](#)  
[Omron Principles](#)  
[Company Profile](#)  
[Business Fields](#)

#### Careers

[Awards](#)  
[Giving Back](#)  
[Summer Internships](#)

#### Contact

[Omron in United States](#)  
[Contact Us](#)  
[Global presence](#)

#### Follow us

[Facebook](#)  
[Twitter](#)

Events  
Giving Back  
Environmental

