



127x127x38mm (5"x 1.5") DC Fan							
Model Number	Speed (RPM)	Max. CFM	Noise (dB)	Volts	Voltage Range	Amps	Max. Static Pressure Inches
OD127AP-12HB	3350	135	48	12	8~14	.99	.32
OD127AP-12HS							
OD127AP-12HTB							
OD127AP-12HTS							
OD127AP-12MB	2800	110	38				
OD127AP-12MS							
OD127AP-12MTB							
OD127AP-12MTS							
OD127AP-12LB	2000	76	30				
OD127AP-12LS							
OD127AP-12LTB							
OD127AP-12LTS							
OD127AP-24HB	3350	140	48	24	11~28	.58	.32
OD127AP-24HS							
OD127AP-24HTB							
OD127AP-24HTS							
OD127AP-24MB	2800	110	38				
OD127AP-24MS							
OD127AP-24MTB							
OD127AP-24MTS							
OD127AP-24LB	2000	76	30				
OD127AP-24LS							
OD127AP-24LTB							
OD127AP-24LTS							
OD127AP-48HB	3350	140	48	48	22~55	.28	.32
OD127AP-48HTB							
OD127AP-48MB	2800	110	38				
OD127AP-48MTB							

OD127AP-48LB

2000

76

30

.15

.18

OD127AP-48LTB

