




RJ45 WE/SS & CATV F Die

Part number: 2687  Technical

Description

Crimps RJ45 WE/SS-style modular plugs and RG6/RG6 Quad CATV "F" connectors.

Features

<UL STYLE="list-style-image: url(\\seba4\Admin\Sourcing\Blocking\Resut ehab 9-7\2687_files\bullet_orange.gif)">

- Fits CrimpALL®/8000 Series and 1300 Series frames.

Crimp style

HEX Crimp

Type

Twisted Pair:
Flat or Round Cable
Solid or Stranded Wire

Coax:
RG6/RG6 Quad Shield

Crimp size

Coax: 0.360/0.324" HEX

Connector style

Western Electric (WE)
Stewart Stamping (SS)

Connector type

RJ45
CATV "F"



[RG6/RG6Q & Cat5e, Cat6 CrimpAll Crimper](#)



[Coax 3-Way Tool](#)



[PowerPlay® PT-525](#)



[Ultimate Technician Tool Kit](#)



[SealTite® Pro for the Smart Home AV Kit](#)