

- [Vises, Work Holding Tools](#)
- [PanaPress, Mini Arbor Press](#)
- [Mobile Electronics Mounts](#)
- [InDash Custom Dash Mounts](#)
- [iPhone/Smartphone Holders-Mounts](#)
- [Smartphone Accessories](#)
- [Mobile Power](#)
- [Action Camera Mounts](#)
- [CCTV, Security Camera Mounts](#)
- [Audio/Video Mounts](#)



Click on any of the above images to find out more about the products pictured.

Model: 381 Vacuum Base PanaVise

The world's most PORTABLE work holding tool!

Quickly attaches to any smooth, non-porous flat surface with the flip of a lever! Take it anywhere you need it for hobbies, electronics and small home repairs.

- Our Vacuum Base PanaVise is widely used for portable applications
- Single knob controls head movement through 3-planes: 90° Tilt, 360° Turn & 360° Rotation
- Jaws are 2.5" (63.5mm) wide, 0.5" (12.6mm) tall and open to 2.25" (57.1mm)
- Nylon jaws offer excellent electrical insulation and gentle holding power (continuous heat tolerance up to 200°F (93°C), intermittent heat to 300°F (149°C)). Interchangeable jaws available
- Base accepts all 300 series Heads and any 5/8" (15.9mm) diameter shaft
- Pad footprint measures 5.125" x 4.25" (130.2mm x 108mm)
- Height: 6.125" (155.6mm), Weight: 2.8 lbs. (1.3kg)



\$74.99

Quantity

[Add To Cart](#)

Accessories Available for the Vacuum Base PanaVise



Model: 203
PV Jr. Head



Model: 304
Low Profile Head



Model: 337
Fixturing Head



Model: 343
Nylon Jaws



Model: 344
Grooved Nylon Jaws



Model: 352
High Heat Jaws



Model: 353
Plated Steel Jaws



Model: 354
Brass Jaws



Model: 366
Wide Opening Head



Model: 376
Self-Centering, Extra Wide Opening Head



Model: 380-RK
Vacuum Base Repair Kit



Model: 385
Micrometer Head

In Use Example for the Vacuum Base PanaVise



When a garage work shop is not available you can use your Model 381 on any smooth non-porous table, including some types of kitchen tables.



Attaches to any smooth, non-porous surface, for example the side of a truck or van.

Related Products



Model: 201
PV Jr.



Model: 209
Vacuum Base PV Jr.



Model: 301
Standard PanaVise



Model: 350
Multi-Purpose Work Center



Model: 396
Wide Opening Head PanaVise