

## 27E629 Product Details



### 27E629

TE Part Number: 4-1393143-8

 [Active](#)

 [Add to Part List](#)

### Relay Sockets and Accessories

 [Converted to EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- Socket
- R10 Series
- Number of Poles = 4
- Terminal Type = PC In-Line
- Terminal Length = 4.57 mm

[View all Features](#) | [Find Similar Products](#)

### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

**NEW!**

### Documentation & Additional Information

#### Product Drawings:

- None Available

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Additional Product Images:

- [Schematic](#)

#### Related Products:

- [Tooling](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- Product Type = Socket
- Terminal Type = PC In-Line
- Body Material = Polyester

#### Body Related Features:

- Series = R10

#### Contact Related Features:

- Number of Poles = 4
- Contact Material = Brass
- Contact Mating Area Plating Material = Tin

#### Configuration Related Features:

- Terminal Length (mm [in]) = 4.57 [0.180]
- Grounding Provision = Without

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Converted to comply with RoHS directive

#### Other:

- Brand = Potter & Brumfield