



0550

Protector

Transport Case

With over 11 cubic feet (0.311 cubic meters) of space, you can store, protect, and move large loads in seconds. The reinforced honeycomb deck and lid construction provide support for heavy equipment, or multiple stacking on a 463L pallet. Opening the case at any altitude is not a problem- the dual integrated automatic pressure equalization valves keep moisture out and prevent vacuum lock, and the double wide grip makes lifting easy. With an IP55 certification, the 0550 Transport Case will protect your gear against rain and dirt. The 0550 Transport Case: Built to move-by forklift, by wheel, by hand.

- **Built to move: by forklift, by wheel or by hand**
- **Fit six 0550 Cases per 463L military pallet, 18 when stacked!**
- **Over 11ft³ (.311m³) of storage space**
- Dual Integrated Automatic Pressure Equalization Valves
- Easy open Double Throw latches
- Four extra-deep base-to-lid locking cleats ensure maximum stacking stability
- Lifetime Guarantee of Excellence
- Locking metal Lidstays keep lid locked in open position
- O-ring seal for dust and water resistant seal (IP55)
- Open cell core with solid wall design - strong, light weight
- Optional Caster Wheel Kit complete with brakes
- Optional Pallet Riser Kit
- Reinforced honeycomb deck and lid for added strength
- Stainless steel hardware and padlock protectors
- Store documents outside the case with our Document Container



CONFIGURATIONS



0550
Standard



0550NF
No Foam



0550WF
With Foam

DIMENSIONS

| | |
|-----------------------------|---|
| Interior (L x W x D) | 47.57 x 24.07" x 17.68 (120.8 x 61.1 x 44.9 cm) |
| Exterior (L x W x D) | 51.05 x 27.54" x 22.79 (129.7 x 70 x 57.9 cm) |
| Lid Depth | 3.19" (8.1 cm) |
| Bottom Depth | 14.49" (36.8 cm) |
| Total Depth | 17.68" (44.9 cm) |
| Int Volume | 11.72 ft ³ (0.332 m ³) |

MATERIALS

Document created on 03-10-19

| | |
|-------------------|--------------------------------|
| Body | Polypropylene |
| Latch | ABS |
| O-Ring | Polymer |
| Pins | Stainless Steel |
| Purge Body | ABS |
| Purge Vent | 3 Micron Hydrophobic Non-Woven |

COLOURS

■ Black

WEIGHT

| | |
|---------------------------|-----------------------|
| Weight With Foam | 95.00 lbs (43.1 kg) |
| Weight Empty | 79.20 lbs (35.9 kg) |
| Buoyancy | 820.00 lbs (371.9 kg) |
| Master Pack Weight | 95.00 lbs (43.1 kg) |

TEMPERATURE

| | |
|----------------------------|-----------------|
| Minimum Temperature | -40°F (-40 °C) |
| Maximum Temperature | 210°F (98.9 °C) |

CERTIFICATIONS

IP57

FOAM PROPERTIES

| | |
|-----------------------|--------------------|
| Layer 1 (Lid) | 3.20" Convolute |
| Layer 2 (Base) | 0.50" Pad |
| Layer 3 (Base) | 3.50" Pick N Pluck |
| Layer 4 (Base) | 3.50" Pick N Pluck |
| Layer 5 (Base) | 3.50" Pick N Pluck |
| Layer 6 (Base) | 3.50" Pick N Pluck |

OTHER

| | |
|--------------------|---|
| Master Pack | 1 |
|--------------------|---|

ACCESSORIES
