

## Insulating sleeve - MPS-IH GY - 0201728

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Insulating sleeve, Color: gray

Illustration of color insulating sleeves for MPS metal part

### Product Features

- Two-piece test plug for individual plug color combinations
- The test plugs are inserted in the function shaft of terminal blocks from the CLIPLINE complete system or in the test connections provided

### Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 017918 099107
Weight per Piece (excluding packing)	0.49 g
Custom tariff number	85472000
Country of origin	Poland

### Technical data

#### Dimensions

Height	15.00 mm
Length	5 mm
Width	5 mm

#### General

Color	gray
Material	PA
Ambient temperature (operation)	-40 °C ... 125 °C

### Standards and Regulations

# Insulating sleeve - MPS-IH GY - 0201728

## Technical data

### Standards and Regulations

Flammability rating according to UL 94	V0
--	----

## Classifications

### eCl@ss

eCl@ss 4.0	27060306
eCl@ss 4.1	27060306
eCl@ss 5.0	27061801
eCl@ss 5.1	27141190
eCl@ss 6.0	27141190
eCl@ss 7.0	27141190
eCl@ss 8.0	27141190

### ETIM

ETIM 2.0	EC000899
ETIM 3.0	EC000899
ETIM 4.0	EC000448
ETIM 5.0	EC002848

### UNSPSC

UNSPSC 6.01	31251501
UNSPSC 7.0901	31251501
UNSPSC 11	31251501
UNSPSC 12.01	31251501
UNSPSC 13.2	31251501

## Approvals

### Approvals

---

Approvals

EAC

---

Ex Approvals

---

Approvals submitted

## Insulating sleeve - MPS-IH GY - 0201728

### Approvals

---

#### Approval details

EAC
-----

---