

Zack Marker strip, flat - ZBF 5/WH-100:UNBEDRUCKT - 0808668

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Zack Marker strip, flat, Strip, white, unlabeled, can be labeled with: Plotter, Mounting type: Snap into flat marker groove, for terminal block width: 5 mm, Lettering field: 5.15 x 5.15 mm

The figure shows the versions
ZBF 5- UNBEDRUCKT, -
LGS:FORTL.ZAHLEN, -
QR:FORTL.ZAHLEN, and -CUS

Product Features

- The ZBF zack marker strip system with flat marker groove is a marking solution for modular terminal blocks and electronics modules
- Other pitches available on request
- The multi-section marking strips are easy to fit and can be easily separated if required
- Labeling service: Phoenix Contact can custom-label all zack marker strip markers according to your requirements
- Unlabeled marking strips can be custom-labeled with a plotter or by hand

Key Commercial Data

| | |
|--------------------------------------|----------|
| Packing unit | 1 pc |
| Minimum order quantity | 100 pc |
| Weight per Piece (excluding packing) | 0.358 g |
| Custom tariff number | 39269097 |
| Country of origin | Germany |

Technical data

Dimensions

| | |
|-----------|------|
| Width (a) | 5 mm |
|-----------|------|

Ambient conditions

| | |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 100 °C |
|---------------------------------|-------------------|

General

| | |
|----------------------------------------|--------------------------------|
| Color | white |
| Components | free from silicone and halogen |
| Flammability rating according to UL 94 | V2 |

Zack Marker strip, flat - ZBF 5/WH-100:UNBEDRUCKT - 0808668

Technical data

General

| | |
|-------------------------------------|------------------------------|
| Material | PA |
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
| Number of individual labels | 10 |
| Number of individual labels per row | 10 |
| Number of marker strips | 10 |
| Marking mounting type | Snap into flat marker groove |

Standards and Regulations

| | |
|----------------------------------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
| Flammability rating according to UL 94 | V2 |

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 24190208 |
| eCl@ss 4.1 | 24190208 |
| eCl@ss 5.0 | 27149103 |
| eCl@ss 5.1 | 27141137 |
| eCl@ss 6.0 | 27141137 |
| eCl@ss 7.0 | 27141137 |
| eCl@ss 8.0 | 27141137 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC000761 |
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC000761 |
| ETIM 5.0 | EC000761 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11 | 39121410 |
| UNSPSC 12.01 | 39121410 |
| UNSPSC 13.2 | 39121410 |