

Marker for terminal blocks - UC-TM 12 - 0819194

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)



Marker for terminal blocks, Sheet, white, unlabeled, can be labeled with: BLUEMARK CLED, BLUEMARK LED, Plotter, Mounting type: Snap into tall marker groove, for terminal block width: 12 mm, Lettering field: 11.45 x 10.5 mm

Product Features

- The UC-TM ... UniCard labeling range includes markers for products with tall marker grooves
- The multi-section marking strips are easy to fit and can be easily separated if required
- The markers, which are supplied in uniform sheets, can be labeled quickly and easily using the BLUEMARK LED
- Labeling service: Phoenix Contact can custom-label all UniCard markers according to your requirements
- The format automatically ensures printing with a high degree of positioning accuracy
- The markers support multi-line labeling
- The sheets provide space for including function texts

Key Commercial Data

| Packing unit | 1 pc |
|--------------------------------------|----------|
| Minimum order quantity | 10 pc |
| Weight per Piece (excluding packing) | 13.63 g |
| Custom tariff number | 39269097 |
| Country of origin | Poland |

Technical data

Dimensions

| Width (a) | 12 mm |
|-----------|-------|
| | |

Ambient conditions

| Ambient temperature (operation) | -40 °C 120 °C |
|---------------------------------|---------------|
|---------------------------------|---------------|

General

| Color | white |
|--|--------------------------------|
| Components | free from silicone and halogen |
| Flammability rating according to UL 94 | V2 |
| Material | PA |



Marker for terminal blocks - UC-TM 12 - 0819194

Technical data

General

| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-------------------------------------|------------------------------|
| Number of individual labels | 40 |
| Number of individual labels per row | 5 |
| Marking mounting type | Snap into tall marker groove |

Standards and Regulations

| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|--|-----------------------------|
| Flammability rating according to UL 94 | V2 |

Classifications

eCl@ss

| eCl@ss 4.0 | 24190208 |
|------------|----------|
| eCl@ss 4.1 | 24190208 |
| eCl@ss 5.0 | 27149103 |
| eCl@ss 5.1 | 27141137 |
| eCl@ss 6.0 | 27141137 |
| eCl@ss 7.0 | 27141137 |
| eCl@ss 8.0 | 27141137 |
| eCl@ss 9.0 | 27141137 |

ETIM

| ETIM 2.0 | EC000761 |
|----------|----------|
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC000761 |
| ETIM 5.0 | EC000761 |

UNSPSC

| UNSPSC 6.01 | 30211811 |
|---------------|----------|
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11 | 39121410 |
| UNSPSC 12.01 | 39121410 |
| UNSPSC 13.2 | 39121410 |

Phoenix Contact 2016 © - all rights reserved http://www.phoenixcontact.com