

## Cable adapter - GW HART USB MODEM - 1003824

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




USB HART modem cable for communication between a PC and HART devices, cable length: 1m.

### Your advantages

- ✔ USB HART modem for commissioning, calibrating, and monitoring HART devices

### Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 472072
GTIN	4055626472072
Weight per Piece (excluding packing)	80.000 g
Custom tariff number	85444290
Country of origin	Germany

### Technical data

#### Dimensions

Fixed cable length	1 m
--------------------	-----

#### Ambient conditions

Ambient temperature (operation)	0 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

#### General

Connection 1	PC side
Connection method	USB 2.0 Fullspeed
Note	serial
Connection 2	Device side
	USB type A (male)
Connection method	Minigrabber

## Cable adapter - GW HART USB MODEM - 1003824

### Technical data

#### General

Number of positions	2
---------------------	---

#### Standards and Regulations

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Noise emission	EN 55032
Noise immunity	EN 55024

### Classifications

#### eCl@ss

eCl@ss 10.0.1	19179290
eCl@ss 6.0	19179200
eCl@ss 7.0	19179290
eCl@ss 9.0	19179290

#### ETIM

ETIM 5.0	EC002584
ETIM 6.0	EC000310
ETIM 7.0	EC000310