

Marker carriers - UBE/D + ES/KMK 3 - 1004076


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Marker carriers, for identifying terminal groups, for mounting on the NS 32 or NS 35/7,5 terminal strip, gray, unlabeled, Mounting type: Plug in, Lettering field: 40 x 17 mm

The figure shows a version of the article

Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 017918 011888
Weight per Piece (excluding packing)	10.5 g
Custom tariff number	39269097
Country of origin	Germany

Technical data

Dimensions

Length (b)	42.5 mm
Width (a)	20 mm
Height	51.5 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
---------------------------------	-------------------

General

Color	gray
Base element material	PA
Components	free from silicone and halogen
Flammability rating according to UL 94	V2
Marking mounting type	Plug in

Standards and Regulations

Marker carriers - UBE/D + ES/KMK 3 - 1004076

Technical data

Standards and Regulations

Flammability rating according to UL 94	V2
--	----

Classifications

eCl@ss

eCl@ss 4.0	24190208
eCl@ss 4.1	24190208
eCl@ss 5.0	27149103
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137
eCl@ss 9.0	27141137

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410