


## Marker carriers - UBE + ES/KMK 3 - 1004089

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Marker carrier, color: Gray for marking groups of terminals, for end clamp E/UK or end clamp E/U, with perforated insert strips, 40 x 17 mm, can be labeled with CMS system

### Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 017918 011895
Weight per Piece (excluding packing)	7.17 g
Custom tariff number	39269097
Country of origin	Germany

### Technical data

#### Dimensions

Length (b)	41.4 mm
Width (a)	20 mm

#### General

Color	gray
Base element material	PA
Components	free from silicone and halogen
Flammability rating according to UL 94	V2
Marking mounting type	Plug in

#### Standards and Regulations

Flammability rating according to UL 94	V2
--	----

## Marker carriers - UBE + ES/KMK 3 - 1004089

### Classifications

#### eCl@ss

eCl@ss 4.0	24190208
eCl@ss 4.1	24190208
eCl@ss 5.0	27149103
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137

#### ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

#### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410