

Multi-function tool - CRIMPFOX 4 IN 1 - 1200101

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)



Tool for processing ferrules according to DIN 46228-4, 0.5 mm² to 2.5 mm², equipped with pressure lock, magazine, cutting, stripping, twisting, and crimping unit.

Product Features

- Integrated pressure lock ensures consistently high-quality crimping
- Up to 30% time savings since the process steps required for assembling conductors can be carried out using only one tool
- Multifunctional crimping pliers for the processing of Taped ferrules according to DIN 46228-4
- Robust and durable due to use of resistant plastics and annealed metals
- Visualized process flows directly on the pliers simplify operation







Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	320.0 g
Custom tariff number	82032000
Country of origin	Germany

Technical data

Dimensions

Length (b)	180 mm
Width (a)	31.5 mm
Height	100 mm

General

Compression	Indent crimp
Type of contact	Ferrules



Multi-function tool - CRIMPFOX 4 IN 1 - 1200101

Technical data

General

Min. AWG, flexible, multi-strand	14
AWG max., flexible, multi-strand	20
Min. cross section	0.5 mm²
Max. cross section	2.5 mm²
AWG min	20
AWG max	14
Maximum stripping length	11 mm

Classifications

eCl@ss

eCl@ss 5.0	21040301
eCl@ss 5.1	21040301
eCl@ss 6.0	21043811
eCl@ss 8.0	21043811
eCl@ss 9.0	21043811

ETIM

ETIM 4.0	EC000168
ETIM 5.0	EC000168

Phoenix Contact 2016 © - all rights reserved http://www.phoenixcontact.com