

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)



Tool for processing ferrules according to DIN 46228-4, 0.5 mm² to 2.5 mm², equipped with pressure lock, cutting, stripping, twisting, and crimping unit, with three magazines including a strip each of ferrules from 0.5 mm² ... 2.5 mm², packaged in a robust plastic case

Your advantages

- ☑ Integrated pressure lock ensures consistently high-quality crimping
- Up to 30% time savings since the process steps required for assembling conductors can be carried out using only one tool
- ☑ Multifunctional crimping pliers for the processing of Taped ferrules according to DIN 46228-4
- Mobust and durable due to use of resistant plastics and annealed metals
- ✓ Visualized process flows directly on the pliers simplify operation



Key Commercial Data

Packing unit	1 pc		
GTIN	4 055626 042398		
GTIN	4055626042398		
Weight per Piece (excluding packing)	720.000 g		
Custom tariff number	82032000		
Country of origin	Germany		

Technical data

Dimensions

Length (b)	180 mm
Width (a)	31.5 mm



Technical data

Dimensions

Height (c)	100 mm
Stripping length	8 mm

General

Compression	Indent crimp
Type of contact	Ferrules
Min. AWG, flexible, multi-strand	14
AWG max., flexible, multi-strand	20
Min. cross section	0.5 mm²
Max. cross section	2.5 mm²
AWG min	20
AWG max	14
Maximum stripping length	11 mm
Weight	600 g
Min. cross section	0.5 mm²
Max. cross section	2.5 mm²
AWG min	20
AWG max	14

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Classifications

eCl@ss

eCl@ss 10.0.1	21043811
eCl@ss 5.0	27400200
eCl@ss 5.1	27400200
eCl@ss 6.0	21043800
eCl@ss 7.0	21043811
eCl@ss 8.0	21043811
eCl@ss 9.0	21043811

ETIM

ETIM 4.0	EC000168
ETIM 5.0	EC000168
ETIM 6.0	EC000168
ETIM 7.0	EC000168



Classifications

UNSPSC

UNSPSC 13.2	27111518
UNSPSC 18.0	27111518
UNSPSC 19.0	27111518
UNSPSC 20.0	27111518
UNSPSC 21.0	27111518

Approvals

Α	a	ıa	o	٧	a	ls
•	~	Μ.	•	•	~	

Approvals

EAC

Ex Approvals

Approval details

EAC

EHE

RU x-DE.xx08.B.02974

Accessories

Accessories

Cable end sleeve

Ferrule - AI 0,5-8 WH S1 - 1200104



Taped ferrules, 0.5 mm², sleeve length 8 mm, with plastic collar, according to DIN 46228-4, white, for processing with the CRIMPFOX 4 IN 1, 10 strips each with 50 sleeves per strip.



Accessories

Ferrule - AI 0,75-8 GY S1 - 1200105



Taped ferrules, 0.75 mm², sleeve length 8 mm, with plastic collar, according to DIN 46228-4, gray, for processing with the CRIMPFOX 4 IN 1, 10 strips each with 50 sleeves per strip.

Ferrule - AI 1,0-8 RD S1 - 1200106



Taped ferrules, 1.0 mm², sleeve length 8 mm, with plastic collar, according to DIN 46228-4, red, for processing with the CRIMPFOX 4 IN 1, 10 strips each with 50 sleeves per strip.

Ferrule - AI 1,5-8 BK S1 - 1200107



Taped ferrules, 1.5 mm², sleeve length 8 mm, with plastic collar, according to DIN 46228-4, black, for processing with the CRIMPFOX 4 IN 1, 10 strips each with 50 sleeves per strip.

Ferrule - AI 2,5-8 BU S1 - 1200108



Taped ferrules, 2.5 mm², sleeve length 8 mm, with plastic collar, according to DIN 46228-4, blue, for processing with the CRIMPFOX 4 IN 1, 10 strips each with 40 sleeves per strip.

Ferrule - AI 0,75-8 BU S1 - 1200163



Ferrule, Dimensions according to DIN 46228-4, with color-coded plastic collars according to NF C 63-023:1994-02, for processing with the CRIMPFOX 4 in 1, sleeve length: 8 mm, length: 14 mm, color: blue, number of strips: 10, number of sleeves per strip: 50



Accessories

Ferrule - Al 2,5-8 GY S1 - 1200164



Ferrule, Dimensions according to DIN 46228-4, with color-coded plastic collars according to NF C 63-023:1994-02, for processing with the CRIMPFOX 4 in 1, sleeve length: 8 mm, length: 14 mm, color: gray, number of strips: 10, number of sleeves per strip: 40

Magazine

Magazine - CRIMPFOX 4 IN 1/MAG - 1200103



Ferrule magazine for CRIMPFOX 4 IN 1, for ferrules with insulating collars from 0.5 mm² ... 2.5 mm², with a length of 8 mm

Phoenix Contact 2020 $\mbox{@}$ - all rights reserved http://www.phoenixcontact.com