

End clamp - E/UK - 1201442

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




End clamp, Width: 9.5 mm, Height: 35.3 mm, Length: 50.5 mm, Color: gray

Product Features

- With universal foot for NS 35 and NS 32 DIN rails
- Tall and low-profile designs
- Large-surface labeling



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	50 pc
GTIN	 4 017918 017323
Weight per Piece (excluding packing)	9.46 g
Custom tariff number	39269097
Country of origin	Germany

Technical data

Dimensions

Height	35.3 mm
Length	50.5 mm
Width	9.5 mm

General

Material	PA
Color	gray
Tightening torque, min	0.4 Nm

End clamp - E/UK - 1201442

Technical data

General

Tightening torque max	0.5 Nm
-----------------------	--------

Standards and Regulations

Flammability rating according to UL 94	V2
--	----

Classifications

eCl@ss

eCl@ss 4.0	27141199
eCl@ss 4.1	27141199
eCl@ss 5.0	27141135
eCl@ss 5.1	27141145
eCl@ss 6.0	27141135
eCl@ss 7.0	27141135
eCl@ss 8.0	27141135

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC001041
ETIM 4.0	EC001041
ETIM 5.0	EC001041

UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	39121708
UNSPSC 11	39121708
UNSPSC 12.01	39121708
UNSPSC 13.2	39121708

Drawings

End clamp - E/UK - 1201442

Dimensional drawing

