

Cover profile carrier - VAH - 1201468

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Adjustable cover holder, for mounting covers (up to 3 mm thick) on terminal blocks, can be used for CLIPFIX 35 and E/UK

Product Features

- Large-surface labeling with AP-ES insert strips
- Cover profiles provide protection against unauthorized actuation of terminal strips



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 017918 017347
Weight per Piece (excluding packing)	8.06 g
Custom tariff number	39269097
Country of origin	Germany

Technical data

General

Color	gray
Flammability rating according to UL 94	V2
Material	PA
Temperature indices (RTI/TI)	125/100

Standards and Regulations

Flammability rating according to UL 94	V2
--	----

Cover profile carrier - VAH - 1201468

Classifications

eCl@ss

eCl@ss 4.0	23150301
eCl@ss 4.1	23150301
eCl@ss 5.0	27141143
eCl@ss 5.1	27141143
eCl@ss 6.0	27379200
eCl@ss 7.0	27141143
eCl@ss 8.0	27149214

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC002498
ETIM 5.0	EC002848

UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	39121708
UNSPSC 11	39121708
UNSPSC 12.01	39121708
UNSPSC 13.2	39121708

Drawings

Cover profile carrier - VAH - 1201468

