


DIN rail, unperforated - NS 35/15 UNPERF 2000MM - 1201714


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



DIN rail, unperforated, Standard profile, width: 35 mm, height: 15 mm, similar to EN 60715, material: Steel, galvanized, passivated with a thick layer, length: 2000 mm, color: silver

RoHS

Key Commercial Data

Packing unit	1 M
Minimum order quantity	5 M
GTIN	 4 017918 017453
GTIN	4017918017453
Weight per Piece (excluding packing)	695.000 g
Custom tariff number	72166190
Country of origin	Germany

Technical data

Dimensions

Height	15 mm
Length	2000 mm
Width	35 mm
Hole width	0.00 mm
Hole height	0.00 mm
Drill hole spacing	0.00 mm

General

Material	Steel
Coating	galvanized, passivated with a thick layer
Color	silver

DIN rail, unperforated - NS 35/15 UNPERF 2000MM - 1201714



Technical data

Standards and Regulations

Test standard	similar to EN 60715
Connection in acc. with standard	IEC / EN

Drawings

Dimensional drawing



DIN rail, unperforated - NS 35/15 UNPERF 2000MM - 1201714

Classifications

eCl@ss

eCl@ss 4.0	27110800
eCl@ss 4.1	27110800
eCl@ss 5.0	27141100
eCl@ss 5.1	27141100
eCl@ss 6.0	27400600
eCl@ss 7.0	27400602
eCl@ss 8.0	27400602
eCl@ss 9.0	27400602

ETIM

ETIM 2.0	EC001285
ETIM 3.0	EC001285
ETIM 4.0	EC000212
ETIM 5.0	EC000212
ETIM 6.0	EC001285
ETIM 7.0	EC001285

UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	39121708
UNSPSC 11	39121708
UNSPSC 12.01	39121708
UNSPSC 13.2	39121708
UNSPSC 18.0	39121708
UNSPSC 19.0	39121708
UNSPSC 20.0	39121708
UNSPSC 21.0	39121708