

DIN rail, unperforated - NS 35/15 AL UNPERF 2000MM - 1201756

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



DIN rail, deep drawn, high profile, unperforated, 1.5 mm thick, material: aluminum, height 15 mm, width 35 mm, length 2000 mm


The illustration shows version NS 35/15-AL without holes with captive slide nut GLM 4

Product Features

- The slide nuts even enable components without an additional snap-on foot to be mounted
- The NS 35/15 AL DIN rail is designed to accommodate GLM ... slide nuts



Key commercial data

Packing unit	2 M
Minimum order quantity	5 M
GTIN	 4 017918 017477
Weight per Piece (excluding packing)	355.0 GRM
Custom tariff number	76042990
Country of origin	Germany

Technical data

Dimensions

Height	15 mm
Length	2000 mm
Width	35 mm

General

Material	Aluminum
Coating	uncoated

DIN rail, unperforated - NS 35/15 AL UNPERF 2000MM - 1201756

Technical data

General

Color	silver
Test standard	Similar to EN 60715: 2001

Classifications

eCl@ss

eCl@ss 4.0	23150301
eCl@ss 4.1	23150301
eCl@ss 5.0	27141143
eCl@ss 5.1	27141143
eCl@ss 6.0	27141143
eCl@ss 7.0	27141143
eCl@ss 8.0	27141143

ETIM

ETIM 2.0	EC001285
ETIM 3.0	EC001285
ETIM 4.0	EC000212
ETIM 5.0	EC000212

UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	39121708
UNSPSC 11	39121708
UNSPSC 12.01	39121708
UNSPSC 13.2	39121708

Drawings

Dimensioned drawing

