

## DIN rail, unperforated - NS 35/15-2,3 UNPERF 2000MM - 1201798


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



DIN rail, material: Steel, unperforated, 2.3 mm thick, height 15 mm, width 35 mm, length: 2 m



### Key commercial data

Packing unit	1 M
Minimum order quantity	5 M
GTIN	 4 017918 017514
Weight per Piece (excluding packing)	910.0 GRM
Custom tariff number	72166190
Country of origin	Germany

### Technical data

#### Dimensions

Height	15 mm
Length	2000 mm
Width	35 mm

#### General

Material	Steel
Coating	Galvanized, passivated with a thick layer
Color	silver
Test standard	In acc. with EN 60715: 2001
Nominal current $I_N$	6000 A

## DIN rail, unperforated - NS 35/15-2,3 UNPERF 2000MM - 1201798

### Classifications

#### eCl@ss

eCl@ss 4.0	27110804
eCl@ss 4.1	27110804
eCl@ss 5.0	27141143
eCl@ss 5.1	27141143
eCl@ss 6.0	27400602
eCl@ss 7.0	27400602
eCl@ss 8.0	27400602

#### ETIM

ETIM 2.0	EC001285
ETIM 3.0	EC001285
ETIM 4.0	EC000212
ETIM 5.0	EC000212

#### UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	39121708
UNSPSC 11	39121708
UNSPSC 12.01	39121708
UNSPSC 13.2	39121708

### Drawings

# DIN rail, unperforated - NS 35/15-2,3 UNPERF 2000MM - 1201798

Dimensioned drawing

