

Tool set - CRIMPSET 6 - 1202072

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Assortment box, metal, supplied with ferrules acc. to DIN 46228-4: 1990-09, 500 pcs. each of AI 0,25-6 YE, AI 0,34-6 TQ, AI 0,5-8 WH, AI 0,75-8 GY, AI 1-8 RD, AI 1,5-8 BK, 300 pcs. AI 2,5-8 BU, 200 pcs. 4-10 GY, 100 pcs. AI 6-12 YE, CRIMPFOX 6T, QUICK WIREFOX 6

Product Features

- We have put together a number of attractive tool sets for you by selecting products from our comprehensive range of professional tools

Key Commercial Data

Packing unit	1 pc
GTIN	 4 017918 017699
Weight per Piece (excluding packing)	2803.0 g
Custom tariff number	82060000
Country of origin	Sweden

Technical data

Dimensions

Length (b)	206 mm
Width (a)	357 mm
Height	48 mm

General

Base element material	Metal
-----------------------	-------

Tool set - CRIMPSET 6 - 1202072

Articles in set

Ferrule - AI 0,25- 6 YE - 3200179



Ferrule, Sleeve length: 6 mm, Length: 10.5 mm, Color: yellow

Ferrule - AI 0,34- 6 TQ - 3009215



Ferrule, Sleeve length: 6 mm, Length: 10.5 mm, Color: turquoise

Ferrule - AI 0,5 - 8 WH - 3200014



Ferrule, Sleeve length: 8 mm, Length: 14 mm, Color: white

Ferrule - AI 0,75- 8 GY - 3200519



Ferrule, Sleeve length: 8 mm, Length: 14 mm, Color: gray

Ferrule - AI 1 - 8 RD - 3200030



Ferrule, Sleeve length: 8 mm, Length: 14 mm, Color: red

Tool set - CRIMPSET 6 - 1202072

Articles in set

Ferrule - AI 1,5 - 8 BK - 3200043



Ferrule, Sleeve length: 8 mm, Length: 14 mm, Color: black

Ferrule - AI 2,5 - 8 BU - 3200522



Ferrule, Sleeve length: 8 mm, Length: 14 mm, Color: blue

Ferrule - AI 4 -10 GY - 3200535



Ferrule, Sleeve length: 10 mm, Length: 17 mm, Color: gray

Ferrule - AI 6 -12 YE - 3200548



Ferrule, Sleeve length: 12 mm, Length: 20 mm, Color: yellow

Stripping pliers - QUICK WIREFOX 6 - 1204384



Stripping tool for cables with PVC insulation, stripping range: 0.08 to 6 mm², wire cutting up to 6 mm² flexible or 4 mm² rigid

Tool set - CRIMPSET 6 - 1202072

Articles in set

Crimping pliers - CRIMPFOX 6T - 1212037



Crimping pliers, for ferrules without insulating collar according to DIN 46228 Part 1 and ferrules with insulating collar according to DIN 46228 Part 4, 0.25 mm² ... 6 mm², lateral entry, trapezoidal crimp

Classifications

eCl@ss

eCl@ss 4.0	21040301
eCl@ss 4.1	21040301
eCl@ss 5.0	21043090
eCl@ss 5.1	21043090
eCl@ss 6.0	21049190
eCl@ss 7.0	21049190
eCl@ss 8.0	27400218

ETIM

ETIM 2.0	EC000149
ETIM 3.0	EC000149
ETIM 4.0	EC000149
ETIM 5.0	EC000524

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Approvals

Approvals

Approvals

EAC

Tool set - CRIMPSET 6 - 1202072

Approvals

Ex Approvals

Approvals submitted

Approval details

EAC
