

Pneumatic crimping tool - ZAP 25 T - 1203123

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Pneumatic crimping pliers, as table top version, for ferrules in accordance with DIN 46228-1: 1992-08 and DIN 46228-4: 1990-09, for conductor cross section 0.25 - 2.5 mm²

Product Features

- These crimping pliers have been specially developed for pre-assembling conductors
- The crimping process is activated by a foot valve
- Two integrated recesses allow quick access to the ferrules



Key Commercial Data

Packing unit	1 pc
GTIN	 4 017918 018092
Weight per Piece (excluding packing)	3079.3 g
Custom tariff number	84678900
Country of origin	Germany

Technical data

Dimensions

Length (b)	190 mm
------------	--------

General

Compression	trapezoidal
Min. AWG, flexible, multi-strand	14
AWG max., flexible, multi-strand	24
Pressure range	4 bar ... 6 bar

Pneumatic crimping tool - ZAP 25 T - 1203123

Technical data

General

Air consumption per compression	0.2 l
---------------------------------	-------

Classifications

eCl@ss

eCl@ss 4.0	21040301
eCl@ss 4.1	21040301
eCl@ss 5.0	21040301
eCl@ss 5.1	21040301
eCl@ss 6.0	17130101
eCl@ss 7.0	17130101
eCl@ss 8.0	21049090

ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001186
ETIM 5.0	EC000168

UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518