

## Crimping pliers - CRIMPFOX ZA 6-3 - 1203301


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Crimping pliers, for insulated cable lugs, 0.14 - 1.0 mm<sup>2</sup> (light green, red), oval crimp



### Key commercial data

Packing unit	1 pc
GTIN	 4 017918 018184
Weight per Piece (excluding packing)	437.9 GRM
Custom tariff number	82032000
Country of origin	Sweden

### Technical data

#### Dimensions

Length (b)	195 mm
------------	--------

#### General

Color	black
Min. AWG, flexible, multi-strand	18
AWG max., flexible, multi-strand	26
Material	Steel with plastic handle

# Crimping pliers - CRIMPFOX ZA 6-3 - 1203301

## Classifications

### eCl@ss

eCl@ss 4.0	21040301
eCl@ss 4.1	21040301
eCl@ss 5.0	21040301
eCl@ss 5.1	21040301
eCl@ss 6.0	21043811
eCl@ss 7.0	21043706

### ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC000168
ETIM 5.0	EC000168

### UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518

## Approvals

### Approvals

---

Approvals

EAC

---

Ex Approvals

---

Approvals submitted

---

### Approval details

EAC
-----

---

