

Crimping pliers - CRIMPFOX MT 2,5 - 1204038

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Crimping pliers, for crimping conductors to the module female contacts STG-MTN, crimp range: 0.5-2.5 mm², AWG: 20-14

Product Features

- Four different die stations
- Optimized mechanical transmission reduces the force required by up to 25%
- Crimping pliers, for crimping conductors to STG-MTN module socket contacts



Key Commercial Data

Packing unit	1 pc
GTIN	 4 017918 018764
Weight per Piece (excluding packing)	820.0 g
Custom tariff number	82032000
Country of origin	Germany

Technical data

Dimensions

Length (b)	270 mm
------------	--------

General

Color	black
Compression	B crimp

Crimping pliers - CRIMPFOX MT 2,5 - 1204038

Classifications

eCl@ss

eCl@ss 4.0	21040301
eCl@ss 4.1	21040301
eCl@ss 5.0	21040301
eCl@ss 5.1	21040301
eCl@ss 6.0	21043811
eCl@ss 7.0	21043811
eCl@ss 8.0	21043811
eCl@ss 9.0	21043811

ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001186
ETIM 5.0	EC000168

UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approvals submitted

Approval details

Crimping pliers - CRIMPFOX MT 2,5 - 1204038

Approvals

EAC
