

## DIN rail perforated - NS 35/15 ZN PERF 2000MM - 1206599

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



DIN rail, material: Galvanized, perforated, height 15 mm, width 35 mm, length: 2 m

### Product Features

If you require greater quantities, the same article is available in a unit pack of 25 pcs. (50 m)



### Key Commercial Data

Packing unit	1 M
Minimum order quantity	5 M
Weight per Piece (excluding packing)	630.0 g
Custom tariff number	72166190
Country of origin	Germany

### Technical data

#### Dimensions

Height	15 mm
Length	2000 mm
Width	35 mm

#### General

Material	Steel
Coating	Galvanized
Color	silver
Test standard	Similar to EN 60715: 2001
Nominal current $I_N$	4200 A

#### Standards and Regulations

Test standard	Similar to EN 60715: 2001
---------------	---------------------------

# DIN rail perforated - NS 35/15 ZN PERF 2000MM - 1206599

## Technical data

### Standards and Regulations

Connection in acc. with standard	IEC / EN
----------------------------------	----------

## Classifications

### eCl@ss

eCl@ss 4.0	27110804
eCl@ss 4.1	27110804
eCl@ss 5.0	27141143
eCl@ss 5.1	27141143
eCl@ss 6.0	27400602
eCl@ss 7.0	27400602
eCl@ss 8.0	27400602
eCl@ss 9.0	27400602

### ETIM

ETIM 2.0	EC001285
ETIM 3.0	EC001285
ETIM 4.0	EC000212
ETIM 5.0	EC000212

### UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	39121708
UNSPSC 11	39121708
UNSPSC 12.01	39121708
UNSPSC 13.2	39121708

## Drawings

## DIN rail perforated - NS 35/15 ZN PERF 2000MM - 1206599

Dimensional drawing

