

## Screwdriver - SZS 1,0X5,5 VDE - 1209114

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Screwdriver, slot-headed, VDE insulated, size: 1.0 x 5.5 x 125 mm, 2-component grip, with non-slip grip

### Product Features

- The tools feature ergonomic two-component safety handles
- Large contact surface of blades inside screw head
- Individually tested safety screwdrivers according to DIN EN 60900 (VDE 0682-201)
- For working on or in the vicinity of live parts up to 1000 V AC or 1500 V DC

### Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	76.0 g
Custom tariff number	82054000
Country of origin	Czech Republic

### Technical data

#### Dimensions

Length (b)	223 mm
Width (a)	33 mm
Blade thickness	1 mm
Blade width	5.5 mm
Blade height	125 mm

#### General

Type	Bladed
	Straight
Material	Alloyed tool steel
Test standard	DIN/ISO 2380-1 IEC 60900:2004

### Standards and Regulations

# Screwdriver - SZS 1,0X5,5 VDE - 1209114

## Technical data

### Standards and Regulations

Test standard	DIN/ISO 2380-1 IEC 60900:2004
---------------	-------------------------------

## Classifications

### eCl@ss

eCl@ss 4.0	21040401
eCl@ss 4.1	21040401
eCl@ss 5.0	21040401
eCl@ss 5.1	21040401
eCl@ss 6.0	21040401
eCl@ss 7.0	21040409
eCl@ss 8.0	21040407

### ETIM

ETIM 3.0	EC000158
ETIM 4.0	EC000158
ETIM 5.0	EC000158

### UNSPSC

UNSPSC 6.01	27111701
UNSPSC 7.0901	27111701
UNSPSC 11	27111701
UNSPSC 12.01	27111701
UNSPSC 13.2	27111701

## Approvals

### Approvals

---

#### Approvals

VDE Zeichengenehmigung / EAC

---

#### Ex Approvals

---

#### Approvals submitted

---

## Screwdriver - SZS 1,0X5,5 VDE - 1209114

### Approvals

#### Approval details

VDE Zeichengenehmigung 

EAC