

DIN rail perforated - NS 35/ 7,5 PERF (18X5,2)2000MM - 1210019


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



NS 35 DIN rail, according to customer specifications, perforated, height: 7,5 mm, width: 35 mm

The illustration shows a version of the product

Key Commercial Data

| | |
|------------------------|---|
| Packing unit | 1 M |
| Minimum order quantity | 5 M |
| GTIN |  4 017918 941970 |
| GTIN | 4017918941970 |
| Custom tariff number | 72166190 |
| Country of origin | Germany |

Technical data

Dimensions

| | |
|--------|---------|
| Height | 7.5 mm |
| Length | 2000 mm |
| Width | 35 mm |

General

| | |
|---------------|---|
| Coating | Galvanized, passivated with a thick layer |
| Color | silver |
| Test standard | In acc. with EN 60715: 2001 |

Standards and Regulations

DIN rail perforated - NS 35/ 7,5 PERF (18X5,2)2000MM - 1210019

Technical data

Standards and Regulations

| | |
|---------------|-----------------------------|
| Test standard | In acc. with EN 60715: 2001 |
|---------------|-----------------------------|