

Torque screwdriver - TSD 20 SAC - 1212020

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Torque screwdriver, with preset torque of 2.0 Nm and 4 mm hexagonal drive for the pressure nut of the fast connection

The figure shows the TSD 04 SAC version

Product Features

- Wide range of SAC... nuts for various different applications
- For the TSD-M... torque screwdrivers, the torque can be custom-set
- The TSD-M... adapters can accommodate the various nuts
- TSD ... SAC torque screwdrivers with a range of preset torques from 0.2 Nm to 2.5 Nm

Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	100.0 g
Custom tariff number	82054000
Country of origin	Czech Republic

Technical data

Dimensions

Length (b)	205 mm
Width (a)	37 mm
Blade height	100 mm

General

Color	black
Type	Hexagonal SW4

Classifications

eCl@ss

eCl@ss 4.0	21040401
------------	----------

Torque screwdriver - TSD 20 SAC - 1212020

Classifications

eCl@ss

eCl@ss 4.1	21040401
eCl@ss 5.0	21040401
eCl@ss 5.1	21040401
eCl@ss 6.0	21040401
eCl@ss 7.0	21040409
eCl@ss 8.0	21040222

ETIM

ETIM 3.0	EC000158
ETIM 4.0	EC000158
ETIM 5.0	EC002132

UNSPSC

UNSPSC 6.01	27111701
UNSPSC 7.0901	27111701
UNSPSC 11	27111701
UNSPSC 12.01	27111701
UNSPSC 13.2	27111701

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approvals submitted

Approval details

EAC
