

## Crimping pliers - CRIMPFOX-RCI 2,5 - 1212053

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Crimping pliers, for insulated cable lugs, 0.5 mm<sup>2</sup> ... 2.5 mm<sup>2</sup> (red, blue), oval crimp

### Product Features

- The color-coded dies clearly indicate the cross section
- Unlockable pressure lock
- They unlock as soon as the required crimping pressure is reached, therefore ensuring sufficient pressure is applied



### Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	440.0 g
Custom tariff number	82032000
Country of origin	Sweden

### Technical data

#### Dimensions

Length (b)	198 mm
Width (a)	18 mm
Height	59 mm

#### General

Color	black
Compression	Oval crimp
Type of contact	Insulated cable lugs
Designation	Crimping position 1
Min. cross section	0.5 mm <sup>2</sup>

## Crimping pliers - CRIMPFOX-RCI 2,5 - 1212053

### Technical data

#### General

Max. cross section	1.5 mm <sup>2</sup>
AWG min	20
AWG max	16
Designation	Crimping position 2
Min. cross section	1.5 mm <sup>2</sup>
Max. cross section	2.5 mm <sup>2</sup>
AWG min	16
AWG max	14
Designation	Crimping position 4
Die station	Crimping position 5

### Classifications

#### eCl@ss

eCl@ss 4.0	21040301
eCl@ss 4.1	21040301
eCl@ss 5.0	21040301
eCl@ss 5.1	21040301
eCl@ss 6.0	21043811
eCl@ss 7.0	21043811
eCl@ss 8.0	21049090

#### ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001186
ETIM 5.0	EC000168

#### UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518

### Approvals

#### Approvals

## Crimping pliers - CRIMPFOX-RCI 2,5 - 1212053

### Approvals

Approvals

EAC

---

Ex Approvals

---

Approvals submitted

---

### Approval details

EAC
-----

### Drawings

Product drawing

