

Crimping pliers - CRIMPFOX-RCI 1 - 1212055

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Crimping pliers, for insulated cable lugs, 0.14 - 1.0 mm² (light green, red), oval crimp

Product Features

- The color-coded dies clearly indicate the cross section
- Unlockable pressure lock
- They unlock as soon as the required crimping pressure is reached, therefore ensuring sufficient pressure is applied



Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	440.0 g
Custom tariff number	82032000
Country of origin	Sweden

Technical data

Dimensions

Length (b)	198 mm
Width (a)	18 mm
Height	59 mm

General

Color	black
Compression	Oval crimp
Type of contact	Insulated cable lugs
Designation	Crimping position 1
Min. cross section	0.14 mm ²

Crimping pliers - CRIMPFOX-RCI 1 - 1212055

Technical data

General

Max. cross section	0.25 mm ²
AWG min	26
AWG max	24
Designation	Crimping position 2
Min. cross section	0.25 mm ²
Max. cross section	0.5 mm ²
AWG min	24
AWG max	22
Designation	Crimping position 3
Min. cross section	0.5 mm ²
Max. cross section	1 mm ²
AWG min	22
AWG max	18

Classifications

eCl@ss

eCl@ss 4.0	21040301
eCl@ss 4.1	21040301
eCl@ss 5.0	21040301
eCl@ss 5.1	21040301
eCl@ss 6.0	21043811
eCl@ss 7.0	21043811
eCl@ss 8.0	21049090

ETIM

ETIM 2.0	EC001186
ETIM 3.0	EC001186
ETIM 4.0	EC001186
ETIM 5.0	EC000168

UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518

Crimping pliers - CRIMPFOX-RCI 1 - 1212055

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approvals submitted

Approval details

EAC

Drawings

Product drawing

