

## Stripping tool - WIREFOX 4 - 1212156

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Stripping tool, for cables and conductors (especially for rubber and silicone insulations) from 0.1 - 4 mm<sup>2</sup>, self-adjusting, stripping length of up to 18 mm, cutting capacity of up to 10 mm<sup>2</sup> stranded/1.5 mm<sup>2</sup> solid, replaceable stripping blade

### Product Description

Insertable stripping blades: 1212152 WIREFOX 10/SB, 1212153 WIREFOX 16/SB, and 1212314 WIREFOX 6SC/SB, direct replacement: 1212151 WIREFOX 4/SB

### Product Features

- Flexible, adjustable limit stop for the stripping length
- WIREFOX ... stripping pliers feature an automatic adjustment mechanism for a wide range of different types of insulation and conductor diameters
- Practical integrated wire cutter

### Key Commercial Data

|                                      |          |
|--------------------------------------|----------|
| Packing unit                         | 1 pc     |
| Weight per Piece (excluding packing) | 220.0 g  |
| Custom tariff number                 | 82032000 |
| Country of origin                    | Sweden   |

### Technical data

#### Dimensions

|                |                   |
|----------------|-------------------|
| Length (b)     | 191 mm            |
| Width (a)      | 20 mm             |
| Height         | 90 mm             |
| Cable diameter | 0.3 mm ... 2.4 mm |

#### General

|       |             |
|-------|-------------|
| Color | Black/green |
|-------|-------------|

### Classifications

eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 21040301 |
|------------|----------|

# Stripping tool - WIREFOX 4 - 1212156

## Classifications

### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.1 | 21040301 |
| eCl@ss 5.0 | 21040301 |
| eCl@ss 5.1 | 21040301 |
| eCl@ss 6.0 | 21043706 |
| eCl@ss 7.0 | 21043706 |
| eCl@ss 8.0 | 21049090 |

### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC001186 |
| ETIM 3.0 | EC001186 |
| ETIM 4.0 | EC000163 |
| ETIM 5.0 | EC000163 |

### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11     | 39121410 |
| UNSPSC 12.01  | 39121410 |
| UNSPSC 13.2   | 39121410 |

## Approvals

### Approvals

---

### Approvals

EAC

---

### Ex Approvals

---

Approvals submitted

---

### Approval details

|     |
|-----|
| EAC |
|-----|

---

